



Main

Range	Clipsal Iconic
Product or component type	Switch
Device application	Lighting
Load type	Fluorescent 10 A LEDi lamp 100 W
Colour tint	Vivid white
Quantity per set	Set of 20

Complementary

Device presentation	Complete product
Control type	Rocker
Device mounting	Flush
Installation direction	Vertical
Switch function	1-pole 1/2-way
Number of rocker	5
Rated current	10 A
[Ue] rated operational voltage	230/240 V
Material	Plastic
Height	120 mm
Width	78 mm
Depth	39 mm
Net weight	0.138 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.8 cm
Package 1 Width	8.7 cm
Package 1 Length	14.6 cm
Package 1 Weight	150 g
Unit Type of Package 2	CAR
Number of Units in Package 2	50
Package 2 Height	33.5 cm
Package 2 Width	26.1 cm
Package 2 Length	33.5 cm
Package 2 Weight	7858.2 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations