

30CSFM-WE

Fan Speed Controller 30 Series Module -
Rotary - 3 speed - 240 V - 75VA - White
Electric



Main

Range of product	Series 30CSFM
Product brand	Clipsal
Device presentation	Basic element
Load type	Capacitive
Colour	White electric

Complementary

Power consumption in VA	75 VA
[Ue] rated operational voltage	220...240 V
Network frequency	50 Hz
Control type	Rotary knob
Mounting support	Wall

Environment

Standards	AS/NZS CISPR 15:2002
-----------	----------------------

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Circularity Profile	End Of Life Information

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.