Product data sheet
Characteristics

30M-MIRROR-WE
Clipsal - Mechanisms, Switch Mechanisms, 30 Series, 10A Mechanisms - Marked, MIRROR

Main

Range of product	Series 30 Standard Series
Product brand	Clipsal
Assembly Type	Basic element

Complementary

Installation Type	Flush
Number Of Switches	1
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Mirror
Marking location	Marking on surface
Actuator	Rocker
Switch function	2-way 1-way

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.36 cm
Package 1 Width	2.36 cm
Package 1 Length	2.9 cm
Package 1 Weight	0.014 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACh Regulation	REACh Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.