



Main

Product brand	Clipsal
Sheath type	Foil + braiding
Colour	External sheath: black

Complementary

Diameter	Conductor: inner: 1.02 mm Conductor: external: 4.57 mm
Material	Inside bare copper conductor Outside aluminium conductor
Cable stiffness	Solid class 1
Cable insulation material	PVC (polyvinyl chloride) PE (polyethylene)
External diameter	7.57 mm
AWG gauge	AWG 18

Environment

Ambient air temperature for operation	80 °C
---------------------------------------	-------

Offer Sustainability

EU RoHS Directive	Not compliant
-------------------	---------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.