



Main

Range of product	Saturn Series
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number Of Outlets	1
Actuator	Rocker Switch
Mounting Type	By screws
Local signalling	Without light indicator
Installation Orientation	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Embedding depth	22 mm
Depth	36 mm
Height	75 mm
Length	116 mm
Width	116 mm
Mounting Centers	84 mm

Environment

Product certifications	RCM
Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.4 cm
Package 1 Width	9 cm
Package 1 Length	11.8 cm
Package 1 Weight	138.4 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations