



Main

Range of product	Saturn Series 4000
Product brand	Clipsal
Assembly Type	Basic element

Complementary

Number of poles	2
Installation Type	Flush
Local signalling	without
[Ue] rated operational voltage	415 V AC
Rated current	32 A
Marking	Without marking
Mounting Type	By screws
Height	116 mm
Width	75 mm
Depth	37 mm
Embedding depth	23 mm
Switch function	2-pole

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.4 cm
Package 1 Width	7.2 cm
Package 1 Length	12 cm
Package 1 Weight	188 g

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes