



Main

Range	Clipsal Iconic
Product or component type	USB charger
[Ue] rated operational voltage	220/240 V AC 50 Hz
Integrated connection type	2 USB 2.0 type A 5 V DC, maximum load current: 2.1 A
Maximum load current with 2 outputs used simultaneously	3.1 A

Complementary

Device mounting	Flush
Device presentation	Mechanism
Colour tint	Vivid white
Surface finish	Glossy
Fixing mode	Clipped
Type of packing	Box
Sale per indivisible quantity	1
Ambient air temperature for operation	0...45 °C
Ambient air temperature for storage	0...60 °C
Relative humidity	5...90 %
Number of terminals	1 with cable end
Height	48 mm
Width	59 mm
Depth	59 mm
Embedding depth	55 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	6.7 cm
Package 1 Length	8.5 cm
Package 1 Weight	107.8 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information