

412L-WE

Standard Series, Single Socket Outlet,
250VAC, 15A, 3 PIN, Surface Mount, Round
Earth Pin



Main

Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Surface
Fixing mode	By screws
Material	Plastic
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Depth	28 mm
Diameter	47 mm
Fixing center	35...38 mm
Number of poles	1

Environment

Standards	AS 3109 AS 3100 AS/NZS 3112
-----------	-----------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	5 cm
Package 1 Length	5 cm
Package 1 Weight	39.6 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	6.8 cm
Package 2 Width	8.4 cm
Package 2 Length	10.8 cm
Package 2 Weight	0.198 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	125

Package 3 Height	25 cm
Package 3 Width	21.4 cm
Package 3 Length	33.8 cm
Package 3 Weight	4.95 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration