



Main

Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
Device mounting	Surface
Fixing mode	By screws
Material	Plastic
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Network frequency	50 Hz
Depth	28 mm
Diameter	47 mm
Fixing center	35...38 mm
Number of poles	1

Environment

Standards	AS 3109 AS 3100 AS/NZS 3112
-----------	-----------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.29 cm
Package 1 Width	0.48 cm
Package 1 Length	0.48 cm
Package 1 Weight	0.045 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	100
Package 2 Height	175 cm
Package 2 Width	285 cm
Package 2 Length	300 cm
Package 2 Weight	100 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration