



Main

Range	Clipsal Iconic
Product or component type	Timer
Device presentation	Mechanism

Complementary

Device mounting	Flush
Actuator	Push-button
Fixing mode	Clip-in
Colour tint	Vivid white
Surface finish	Matt
Connections - terminals	Screw terminals
Type of packing	Box
Sale per indivisible quantity	1
Remote control type	Wiser room application
[Ue] rated operational voltage	220...240 V AC 50 Hz
Operating distance	30 m
Control signal type	ControlLink
Connections - terminals	Screw terminals
Number of terminals	2
Wiring configuration	2-wire
Material	PC (UL94 V-2): top PC MAS056 (UL94 V-2): bottom
Height	22 mm
Width	22 mm
Depth	40 mm
Embedding depth	38 mm
Standards	AS/NZS 60669.2.1

Environment

Ambient air temperature for storage	0...60 °C
Ambient air temperature for operation	0...45 °C
Relative humidity	0...90 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.9 cm
Package 1 Width	6.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	41 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information