



Main

Product or component type	Residual current circuit breaker (RCCB)
Product brand	Clipsal
Poles description	4P
Number of modules	4
[In] rated current	40 A
Earth-leakage sensitivity	30 mA
Earth-leakage protection class	Type A-SI

Complementary

[Ue] rated operational voltage	415 V AC
[Uimp] rated impulse withstand voltage	6 kV
Mounting support	DIN rail
Size	81 x 72 x 75 mm conforming to DIN 43880

Environment

Standards	AS/NZS 61008
IP degree of protection	IP40
Pollution degree	2
Ambient air temperature for operation	-5...40 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations