



Main

Range	MAX4
Product or component type	Residual current breaker with overcurrent protection (RCBO)
Product brand	Clipsal
Poles description	2P
Number of modules	2
[In] rated current	32 A
Curve code	C
Earth-leakage sensitivity	10 mA
Earth-leakage protection class	Type A
Breaking capacity	6000 A

Complementary

[Ue] rated operational voltage	240 V AC
[Uimp] rated impulse withstand voltage	4 kV
Size	81 x 36 x 77.5 mm conforming to DIN 43880

Environment

Standards	AS/NZS 61009
IP degree of protection	IP20 IP40
Ambient air temperature for operation	-5...40 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	10.2 cm
Package 1 Length	4.1 cm
Package 1 Weight	211.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Sustainable packaging	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations