






Main

Range	C-Bus
Product brand	Clipsal
Product or component type	Power supply
Device application	Power supply

Complementary

Secondary voltage	32...39 V DC
Output current	<= 350 mA
[Us] rated supply voltage	240 V AC 50 Hz
Supply circuit type	AC
Number of lines feed	1
Number of modules	4
Local signalling	LED

Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.