



Main

Range of product	Series 56
Product brand	Clipsal

Complementary

[Us] rated supply voltage	Lamp: 250 V AC
[In] rated current	10 A
Colour	Grey
Cap/operator or lens colour	Red/green
Width	101 mm opening:
Height	107 mm opening:
Depth	80 mm opening:
Marking	START-STOP

Environment

IP degree of protection	IP66
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.5 cm
Package 1 Width	10.5 cm
Package 1 Length	11.0 cm
Package 1 Weight	366.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	24
Package 2 Height	21.0 cm
Package 2 Width	34.8 cm
Package 2 Length	44.5 cm
Package 2 Weight	8.784 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations