



Main

Range	Clipsal - 56 Series
Range of product	Series 56
Product brand	Clipsal
Product or component type	Appliance inlet
Device application	Power supply

Complementary

[In] rated current	10 A
Poles description	3P + N + E
[Ue] rated operational voltage	500 V 50/60 Hz conforming to EN 60309-2
Colour	Electric orange (RAL 2004)
Material	Plastic
Plug, socket category	Low voltage
Material	Polycarbonate: cover
Mounting mode	Surface mounted
Outlet standard	Australian/New Zealand
Outlet standard	Industrial
Tightening torque	0.8 N.m
Connections - terminals	Screw terminal 1.5...6 mm ² rigid or stranded cable
Contacts material	Screws: brass
Plug, socket, control station shape	Angled
Duration	7 h
Net weight	0.817 kg
Height	204 mm
Width	101 mm
Depth	138 mm
Targeted country	Australia

Environment

Standards	AS/NZS 60320.1
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C

Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration