



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet with residual current device
Device application	Power supply
Colour	Grey (RAL 7035)

Complementary

Number of poles	3
Control type	Push-button
Number of power socket outlets	1 protective cover
[In] rated current	15 A
[Ue] rated operational voltage	250 V AC 50 Hz
Network number of phases	1 phase
Number of gangs	2 gangs
Installation direction	Vertical
Device mounting	Surface
Material	Polycarbonate
Connections - terminals	Screw terminals cable(s) 1...6 mm ²
Depth	102 mm
Width	101 mm
Height	204 mm
Net weight	0.96 kg
Targeted country	Australia

Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66
Earth-leakage protection class	Type A
Electrical insulation class	Class II

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.6 cm
Package 1 Width	10.8 cm
Package 1 Length	20.8 cm
Package 1 Weight	1.006 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Height	30.5 cm

Package 2 Width	29.6 cm
Package 2 Length	43.6 cm
Package 2 Weight	12.072 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	324
Package 3 Height	106.5 cm
Package 3 Width	116.5 cm
Package 3 Length	116.5 cm
Package 3 Weight	345040 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes