



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet
Device application	Power supply
Colour	Grey (RAL 7035)

Complementary

Number of poles	4
Plug, socket category	Low voltage
Outlet standard	Australian/New Zealand
Plug, socket, control station shape	Straight
Number of modules	3
Number of power socket outlets	1 protective cover
[In] rated current	50 A
[Ue] rated operational voltage	500 V AC 50 Hz
Poles description	3P + E
Protection type	Without protection
Device mounting	Surface
Material	Polycarbonate: cover
Contacts material	Pins: phosphor bronze
Connections - terminals	Screw terminals cable(s) 10...16 mm ²
Electrical connection	Industrial connector
Depth	108 mm
Width	101 mm
Height	204 mm
Targeted country	Australia

Environment

Standards	AS/NZS 3123 AS/NZS 3133
Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.0 cm
Package 1 Width	10.0 cm
Package 1 Length	20.5 cm
Package 1 Weight	1245.0 g
Unit Type of Package 2	CAR

Number of Units in Package 2	8
Package 2 Height	21.4 cm
Package 2 Width	29.7 cm
Package 2 Length	42.9 cm
Package 2 Weight	9.99 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes