



## Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switched socket
Device application	Power supply
Colour	Grey
Outlet standard	Australian/New Zealand

## Complementary

Plug, socket category	Low voltage
Plug, socket, control station shape	Straight Angled
Mounting mode	Surface mounting
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC 50 Hz conforming to EN 60309-2
Poles description	1P + N + E
Voltage colour	Blue
Protection type	Without protection
Duration	6 h
Material	Polycarbonate: cover
Contacts material	Pins: phosphor bronze
Connections - terminals	Screw terminals 1.5...6 mm <sup>2</sup>
Depth	85 mm
Width	101 mm
Height	204 mm
Targeted country	Australia

## Environment



IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Standards	AS/NZS 3112 AS/NZS 4417.1

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.85 cm
Package 1 Width	10.35 cm
Package 1 Length	20.65 cm
Package 1 Weight	758.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	12
Package 2 Height	21.4 cm
Package 2 Width	29.7 cm

Package 2 Length	42.9 cm
Package 2 Weight	9.52 kg

## Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>