



## Main

|                           |                     |
|---------------------------|---------------------|
| Range                     | Clipsal - 56 Series |
| Range of product          | Series 56           |
| Product brand             | Clipsal             |
| Product or component type | Plug                |
| Device application        | Power supply        |

## Complementary

|                                     |                                         |
|-------------------------------------|-----------------------------------------|
| [In] rated current                  | 10 A                                    |
| Poles description                   | 3P + E                                  |
| [Ue] rated operational voltage      | 500 V AC 50 Hz conforming to EN 60309-2 |
| Colour                              | Orange (RAL 2004)                       |
| Material                            | Plastic                                 |
| Plug, socket category               | Low voltage                             |
| Material                            | Polycarbonate: housing                  |
| Outlet standard                     | Industrial                              |
| Connections - terminals             | Screw terminal 1...6 mm <sup>2</sup>    |
| Wire stripping length               | 45 Mm<br>12 mm                          |
| Contacts material                   | Pins: brass                             |
| Cable entry                         | Cable gland                             |
| Thread type                         | M25                                     |
| Plug, socket, control station shape | Straight                                |
| Pin arrangement                     | K                                       |
| Duration                            | 7 h                                     |
| Net weight                          | 0.36 kg                                 |
| Height                              | 78 mm                                   |
| Width                               | 78 mm                                   |
| Depth                               | 167 mm                                  |
| Targeted country                    | Australia                               |

## Environment

|                                       |                             |
|---------------------------------------|-----------------------------|
| Standards                             | AS/NZS 3123                 |
| IP degree of protection               | IP66 conforming to AS 60529 |
| Ambient air temperature for operation | -25...75 °C                 |

## Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | PCE     |
| Number of Units in Package 1 | 1       |
| Package 1 Height             | 8.4 cm  |
| Package 1 Width              | 9.8 cm  |
| Package 1 Length             | 17.6 cm |
| Package 1 Weight             | 312.0 g |

## Offer Sustainability

|                            |                                                                                                                                 |
|----------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                           |
| REACH Regulation           | <a href="#"> REACH Declaration</a>             |
| EU RoHS Directive          | Compliant with Exemptions                                                                                                       |
| China RoHS Regulation      | <a href="#"> China RoHS Declaration</a>        |
| RoHS exemption information | <a href="#"> Yes</a>                           |
| Environmental Disclosure   | <a href="#"> Product Environmental Profile</a> |
| Circularity Profile        | No need of specific recycling operations                                                                                        |