

56PA550-EO

Clipsal - 56 Series, Plugs and Extension
Sockets, Angle Plugs - IP66, 500V 50A - 5
Round Pins



Main

| | |
|---------------------------|---------------------|
| Range | Clipsal - 56 Series |
| Range of product | Series 56 |
| Product brand | Clipsal |
| Product or component type | Plug |
| Device application | Power supply |

Complementary

| | |
|-------------------------------------|---|
| [In] rated current | 50 A |
| Poles description | 3P + N + E |
| [Ue] rated operational voltage | 500 V AC 50 Hz conforming to EN 60309-2 |
| Colour | Orange (RAL 2004) |
| Material | Plastic |
| Plug, socket category | Low voltage |
| Material | Polycarbonate: housing |
| Outlet standard | Industrial |
| Connections - terminals | Screw terminal 2.5...25 mm ² |
| Wire stripping length | 50 Mm 20 mm |
| Contacts material | Pins: brass |
| Cable entry | Cable gland |
| Thread type | M40 |
| Plug, socket, control station shape | Angled |
| Pin arrangement | U |
| Duration | 7 h |
| Net weight | 0.42 kg |
| Height | 78 mm |
| Width | 130 mm |
| Depth | 168 mm |
| Targeted country | Australia |

Environment

| | |
|---------------------------------------|-----------------------------|
| Standards | AS/NZS 3123 |
| IP degree of protection | IP66 conforming to AS 60529 |
| Ambient air temperature for operation | -25...75 °C |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 9.0 cm |
| Package 1 Width | 9.4 cm |
| Package 1 Length | 20.0 cm |
| Package 1 Weight | 444.0 g |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| EU RoHS Directive | Compliant with Exemptions |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |
| Environmental Disclosure |  Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |