



Main

Range	Clipsal - 56 Series
Product or component type	Socket-outlet with residual current device
Device application	Power supply
Colour	Grey (RAL 7035)

Complementary

Control type	Push-button
[In] rated current	40 A
[Ue] rated operational voltage	500 V AC 50 Hz
Network number of phases	3 phases
Number of gangs	4 gangs
Installation direction	Vertical
Material	Polycarbonate
Connections - terminals	Screw terminal cable(s) 10...16 mm ²
Mounting mode	Surface mounted
Depth	135 mm
Width	204 mm
Height	204 mm
Net weight	2.34 kg
Targeted country	Australia

Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations