



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Socket-outlet
Device application	Power supply
Colour	Grey (RAL 7035)
Outlet standard	Australian/New Zealand

Complementary

Number of poles	2
Plug, socket category	Low voltage
Plug, socket, control station shape	Straight
Device mounting	Surface
Mounting mode	External mounting
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC 50 Hz conforming to EN 60309-2
Poles description	1P + N + E
Voltage colour	Blue
Duration	6 h
Material	Polycarbonate: cover
Contacts material	Screws: brass
Connections - terminals	Screw terminals 1.5...6 mm ² rigid or stranded cable
Connections - terminals	Screw terminal
Tightening torque	0.8 N.m
Socket number	1
Socket-outlet type	A
Outlet standard	Industrial
Cable outer diameter	9...29 mm
Net weight	0.222 kg
Depth	64 mm
Width	101 mm
Height	107 mm
Targeted country	Australia

Environment

IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Standards	AS/NZS 3112 AS/NZS 4417.1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.65 cm
Package 1 Width	9.95 cm
Package 1 Length	9.95 cm
Package 1 Weight	227.0 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes