



Main

Range	Clipsal - 56 Series
Product or component type	Socket-outlet
Device application	Power supply
Colour	Grey (RAL 7035)

Complementary

Plug, socket category	Low voltage
Mounting mode	Surface mounted
[In] rated current	16 A
[Ue] rated operational voltage	500 V AC 50 Hz
Poles description	3P + N + E
Secondary keyway clockwise position	6 h
Material	Polycarbonate: cover
Contacts material	Screws: brass
Connections - terminals	Screw terminals rigid or stranded cable
Tightening torque	0.8 N.m
Outlet standard	Industrial
Net weight	0.292 kg
Length	107 mm
Width	101 mm
Targeted country	Australia


Environment

IP degree of protection	IP66 conforming to IEC 60529
Ambient air temperature for operation	-25...75 °C
Standards	IEC 309-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.5 cm
Package 1 Width	10.5 cm
Package 1 Length	10 cm
Package 1 Weight	0.292 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes