



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switch
Assembly Type	Basic element with full cover plate
Device application	Control
Handle colour	Red
Suitability for isolation	Yes
Colour	Cover: grey

Complementary

Poles description	4P
Control type	Rotary knob
Number of poles	4
Installation Type	Surface
Material	PC (polycarbonate)
Tightening torque	0.8 N.m
Local signalling	without
[Ue] rated operational voltage	500 V AC 50 Hz
Rated current	40 A
Marking	Without marking
Mounting Type	By screws
Breaking capacity	40 kA
Targeted country	Australia
Height	204 mm
Width	101 mm
Depth	172 mm
Net weight	1.24 kg
Motor M-rating AS3133	M220 at 690 V
Switch function	4-pole
Rotary handle padlocking	2 padlocks 8 mm

Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.7 cm
Package 1 Width	21.2 cm
Package 1 Length	21.5 cm
Package 1 Weight	1.157 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations