



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Time switch
Device presentation	Basic element with full cover plate
Device application	Control
Colour	Grey (RAL 7035)
Plug, socket category	Low voltage
Outlet standard	Australian/New Zealand

Complementary

Poles description	1P + N + E
Device mounting	Surface
Plug, socket, control station shape	Straight Angled
Material	Polycarbonate: cover
Contacts material	Pins: phosphor bronze
Local signalling	without
[Ue] rated operational voltage	250 V AC 50 Hz
Rated current	16 A
Protection type	Without protection
Marking	Without marking
Height	101 mm
Width	101 mm
Net weight	0.001 kg
Targeted country	Australia




Environment

Ambient air temperature for operation	-25...75 °C
Outlet standard	Industrial
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133 AS/NZS 3123

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.001 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes