



Main

Range of product	600 Series
Product or component type	Illuminated module

Complementary

Material	PC (polycarbonate)
Light source colour	Red
Colour tint	White
Surface finish	Opaque
Installation direction	Vertical
Length	23 mm
Width	23 mm
Depth	25 mm
[Ue] rated operational voltage	24 V
Network type	AC/DC
Network number of phases	1 phase
Number of gangs	1 gang
Mounting mode	Front
Number of terminals	3
Cut-out dimensions	25 mm
Quantity per set	Set of 20
Type of packing	Crate

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Circularity Profile	End Of Life Information