



Main

Range of product	Series 66P
Product brand	Clipsal

Complementary

[In] rated current	63 A
[Ue] rated operational voltage	500 V 50/60 Hz conforming to EN 60309-2
Material	Plastic
Connections - terminals	Screw terminal
Cable entry	Cable gland
Plug, socket, control station shape	Straight
Duration	7 h

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Circularity Profile	No need of specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.