Product data sheet
Characteristics

67P332/6
67 Series, Plug Top, Straight, 3 PIN, 32A, IP67

Main

Range of product	Series 67
Product brand	Clipsal

Complementary

[In] rated current	32 A
[Ue] rated operational voltage	230 V 50/60 Hz conforming to EN 60309-2
Cable entry	Cable gland
Plug, socket, control station shape	Straight
Duration	6 h

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.8 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACh Regulation	REACh Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.