



Main

Range of product	ARGUS standard movement detector
Range	ARGUS
Product or component type	Presence detector with IR receiver
Load type	Halogen lamp: 1000 W, AC Incandescent lamp: 1000 W, AC Compact fluorescent lamp: 3 x 23 W, AC Fluorescent lamp: 200 VA, AC
Colour tint	White

Complementary

[Ue] rated operational voltage	220...240 V
Network frequency	50/60 Hz
[Ue] rated operational voltage	220...240 V
Number output current	10 A
Number of channels	1
Control type	Movement sensor
Function available	Switching, toggling, dimming
Light intensity adjustment	5...1000 lux
Horizontal detection angle	360 °
Cable length	0.035 m
Detection range	Radius
Material	ABS + PC matt
Device mounting	Ceiling
Mounting height	2.5 m


Environment

IP degree of protection	IP20
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.4 cm
Package 1 Width	12.6 cm
Package 1 Length	13.2 cm
Package 1 Weight	254.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Circularity Profile	No need of specific recycling operations