



### Main

Range	Acti 9
Product or component type	Comb busbar
Accessory / separate part category	Connection accessory
Lines description	3L + N
Length in 18 mm modules	57

### Complementary

Number of ways	38 ways Aux + N + L
Poles configuration for 1 way	1 x 1P
Connection pitch	18 mm
Connector type	Tooth
Distance between way	27 mm
Marking	L1 L2 L3
Insulation	Insulated
Device presentation	Cuttable
Provided equipment	Set of 10 end piece
[Ie] rated operational current	100 A at 40 °C
[Ue] rated operational voltage	415 V AC
[Ui] rated insulation voltage	500 V AC conforming to IEC 61439-2
Mounting mode	Horizontal
Mounting location	Top or bottom on tunnel type terminals Top or bottom on double terminal
9 mm pitches	114
Width	1000 mm
Colour	White (RAL 9003)
Range compatibility	Acti 9 iC60 Acti 9 iK60 Acti 9 iID Acti 9 iID K Acti 9 iSW Acti 9 iSW-NA Multi 9 C60

### Environment

Standards	IEC 60947-7-1 IEC 61439-2
Fire resistance	960 °C ( 30 s ) conforming to IEC 60695-2-1
Pollution degree	3 conforming to IEC 60947-7-1
IP degree of protection	IP20 with end-pieces and tooth covers

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------