



Main

Product or component type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	Spacial S3D Spacial CRN Thalassa PLA Thalassa PLS Thalassa PLM
Device composition	Without cover
Quantity per set	Set of 8

Complementary

Colour	Blue (RAL 5000)
Fixing mode	By screws Clip-on support
Material	PVC (polyvinyl chloride)
Height	35 mm
Length	2000 mm
Width	30 mm
Net weight	0.5 kg
Total number of wires	60

Environment



Ambient air temperature for operation	-5...60 °C
Flame retardance	V-0 conforming to UL 94
Fire resistance	960 °C conforming to IEC 60695-2-1/1
Standards	VDE 0506 VDE 0660 DIN 43659 NF C 68-102

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	200.0 cm
Package 1 Width	8.0 cm
Package 1 Length	7.0 cm
Package 1 Weight	487.0 g
Unit Type of Package 2	PAL
Number of Units in Package 2	240
Package 2 Height	77.0 cm
Package 2 Width	280.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	129.0 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	8
Package 3 Height	7.5 cm

Package 3 Width	8.5 cm
Package 3 Length	200.0 cm
Package 3 Weight	3.9 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------