



Main

Product or component type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	Spacial S3D Spacial CRN Thalassa PLA Thalassa PLS Thalassa PLM
Device composition	Without cover
Quantity per set	Set of 8

Complementary

Colour	Blue (RAL 5000)
Fixing mode	By screws Clip-on support
Material	PVC (polyvinyl chloride)
Height	90 mm
Length	2000 mm
Width	30 mm
Net weight	1.12 kg
Total number of wires	200

Environment



Ambient air temperature for operation	-5...60 °C
Flame retardance	V-0 conforming to UL 94
Fire resistance	960 °C conforming to IEC 60695-2-1/1
Standards	VDE 0506 DIN 43659 NF C 68-102 VDE 0660

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	18.5 cm
Package 1 Width	8.5 cm
Package 1 Length	200.0 cm
Package 1 Weight	1.675 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	8.5 cm
Package 2 Width	18.5 cm
Package 2 Length	200.0 cm
Package 2 Weight	13.4 kg
Unit Type of Package 3	P2M
Number of Units in Package 3	336
Package 3 Height	120 cm

Package 3 Width	202 cm
Package 3 Length	70 cm
Package 3 Weight	235 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------