



### Main

Product brand	Clipsal
Range of product	Blue Point

### Complementary

Cable cross section	4 mm <sup>2</sup> fine stranded without cable end sleeve
[In] rated current	20 A
Connector type	1 screw terminals 2 screw terminals
Number of poles	12
Mounting support	Panel
Material	Bakelite: insulation
Width	17 mm grid pattern:
Minimum mounting height	16 mm
Length	122 mm

### Environment

Ambient air temperature for operation	190 °C
---------------------------------------	--------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	1.8 cm
Package 1 Length	12.1 cm
Package 1 Weight	48.4 g

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations