



Main

Product brand	Clipsal
Range of product	Blue Point

Complementary

Cable cross section	4 mm ² fine stranded without cable end sleeve
[In] rated current	30 A
Connector type	1 screw terminals 2 screw terminals
Number of poles	12
Mounting support	Panel
Material	Nylon: insulation
Width	20 mm grid pattern:
Minimum mounting height	16 mm
Length	117 mm

Environment

Ambient air temperature for operation	120 °C
Standards	CS/840/N

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	1.8 cm
Package 1 Length	12.2 cm
Package 1 Weight	35.7 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations