



Main

Range	Clipsal
Product or component type	Batten light
Device application	Lighting
Market segment	Small commercial Residential

Complementary

Type of installation	Indoor
Total system power	20 W
Power factor	0.9
Light source	LED 20 W
[Ue] rated operational voltage	240 V AC 50 Hz
Luminous flux	2200 lm
Bulb lifespan	36000 h
Colour temperature	4000 K
Beam angle	110 °
Device mounting	Surface
Mounting mode	Surface mounting
IP degree of protection	IP20
Electrical insulation class	Class I
Length	615 mm
Width	120 mm
Height	30 mm
Shape	Rectangular
Net weight	2.0 kg

Environment

Colour rendering index	R _a =80
Ambient air temperature for operation	-10...40 °C
Relative humidity	10...95 % non-condensing

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.7 cm
Package 1 Width	12.6 cm
Package 1 Length	63 cm
Package 1 Weight	2 kg

Contractual warranty

Warranty	3-Year
----------	--------