



Main

Product or component type	Connector
Accessory / separate part category	Connection accessory
Product compatibility	Plug Easy56 EY56P315
Plug, socket category	Low voltage
Poles description	1P + N + E
Pin number	3 pins
Shape of pin	Flat
Network type	AC
Outlet standard	Australian/New Zealand

Complementary

Plug, socket, control station shape	Straight
[In] rated current	15 A
[Ue] rated operational voltage	250 V
Network frequency	50 Hz
Material	Polycarbonate: housing
Contacts material	Sleeves: brass
Connections - terminals	Screw terminals
Cable cross section	1.5 mm ²
Wire stripping length	12...34 mm
Cable outer diameter	7.4...10.6 mm
Cable entry	Cable gland
Thread type	M20
Net weight	0.107 kg
Height	65 mm
Width	65 mm
Depth	105 mm
Colour	Plug: orange (RAL 2004) Body: clear

Environment

Standards	AS/NZS 3120
Quality labels	RCM
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Ambient air temperature for storage	-25...75 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	6.2 cm
Package 1 Length	10.8 cm
Package 1 Weight	123 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations