



Main

Product name	Easy56
Product or component type	Socket-outlet
Device short name	EY56SO310
Plug, socket category	Low voltage
Poles description	1P + N + E
Network type	AC
Outlet standard	Australian/New Zealand

Complementary

Mounting mode	Surface mounted
Plug, socket, control station shape	Straight
[In] rated current	10 A
Pin number	3 pins
Shape of pin	Flat
[Ue] rated operational voltage	250 V
Network frequency	50 Hz
Material	Polycarbonate: cover
Contacts material	Pins: phosphor bronze
Connections - terminals	Screw terminals 1.5...6 mm ² rigid or stranded cable
Wire stripping length	10 mm
Net weight	0.471 kg
Height	101 mm
Width	101 mm
Depth	101 mm
Colour	Grey (RAL 7035)

Environment

Standards	AS/NZS 3112
Quality labels	RCM
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Ambient air temperature for storage	-25...75 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.2 cm
Package 1 Width	10.2 cm
Package 1 Length	10.6 cm
Package 1 Weight	380.0 g

Offer Sustainability

EU RoHS Directive	Under investigation
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations