



## Main

Range of product	OptiLine 70
Cabling installation system	Trunking
Product or component type	Installation trunking
Colour tint	Polar white (RAL 9003)
Quantity per set	12 m

## Complementary

Trunking material	Plastic
Trunking dimension	120 x 55 mm
Compartment partitioning	1 compartment
Fixing mode	By screws
Front opening size	70 mm
Material	PVC (polyvinyl chloride)
Length	2000 mm
Height	120 mm
Width	55 mm

## Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-2-1:2002
Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	2
Package 1 Height	5.5 cm
Package 1 Width	12.0 cm
Package 1 Length	200.0 cm
Package 1 Weight	2.04 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	12.0 cm
Package 2 Width	25.0 cm
Package 2 Length	204.0 cm
Package 2 Weight	12.51 kg
Unit Type of Package 3	PAL

Number of Units in Package 3	156
Package 3 Height	62.0 cm
Package 3 Width	120.0 cm
Package 3 Length	210.0 cm
Package 3 Weight	183.0 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations