



### Main

Range of product	OptiLine 70
Cabling installation system	Trunking
Product type	Internal corner
Colour	Aluminium metallic
Quantity package 1 / unit	Set of 1

### Complementary

Trunking material	Aluminium
Trunking dimension	120 x 55 mm
Fixing mode	Snap-fitted
Product material	PC/ABS painted
Length	117 mm
Height	129 mm
Width	117 mm

### Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating temperature	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

### Contractual warranty

Warranty	18 months
----------	-----------