



### Main

Cabling installation system	Pole Post
Product or component type	Cable feeder

### Complementary

Type of pole	One installation box Two installation boxes Two-sided One-sided
Type of post	One-sided Two-sided
Colour tint	Grey (RAL 7030)
Quantity per set	Set of 10
Pole/post surface finish	Powder coated Anodized
Pole fixing mode	Tension-mounted
Fixing mode	Snap-fitted
Material	PVC (polyvinyl chloride)
Length	120 mm
Height	20 mm
Width	120 mm
Market segment	Small commercial Residential

### Environment

Standards	EN 50085-1:2005 NF C 68-102
Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP30

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

---

Warranty	18 months
----------	-----------

---