



Main

Range	TeSys
Device short name	KCF2
Product or component type	Rotary handle
Product compatibility	V3 V4
Handle colour	Red

Complementary

Handle front plate colour	Yellow
Rotary handle padlocking	1 to 3 padlocks 4...8 mm
Marking	0 - 1
Fixing mode	By 4 screws
Handle front plate dimension	60 x 60 mm
Height	60 mm
Width	60 mm
Net weight	0.07 kg

Environment

IP degree of protection	IP65
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	7.000 cm
Package 1 Length	8.500 cm
Package 1 Weight	74.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	45
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.854 kg
Unit Type of Package 3	P06
Number of Units in Package 3	360
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	43.755 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------