



### Main

Range	Acti 9
Product or component type	Load Centre
Device application	Distribution
Provided equipment	Enclosure DIN rail

### Complementary

Number of poles	12
Material	Steel
Colour	Grey
Number of horizontal rows	1
Number of 18 mm modules per row	12
Type of rail	DIN
Mounting plate description	Without mounting plate
Height	231 mm
Width	346 mm
Depth	66 mm
Enclosure mounting	Surface

### Environment

IP degree of protection	IP40
-------------------------	------

### Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.