



Main

Product brand	Clipsal
---------------	---------

Complementary

Curve code	B
Number of poles	1
[In] rated current	32 A
Number of modules	1
[Ue] rated operational voltage	240 V
Breaking capacity	6 kA conforming to EN 60898
Network type	AC
Network frequency	50/60 Hz

Environment

IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-5...40 °C
Standards	IEC 60898
Product certifications	CE: N17682[RETURN]ACMA: N11193[RETURN]RCM: N5400

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.2 cm
Package 1 Width	1.8 cm
Package 1 Length	8.5 cm
Package 1 Weight	0.117 kg

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes