



## Main

Product brand	Clipsal
---------------	---------

## Complementary

Curve code	C
Number of poles	1
[In] rated current	63 A
Number of modules	1
[Ue] rated operational voltage	240 V
Breaking capacity	6 kA conforming to EN 60898
Network type	AC
Network frequency	50/60 Hz

## Environment

IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-5...40 °C
Standards	IEC 60898
Product certifications	CE: N17682[RETURN]ACMA: N11193[RETURN]RCM: N5400

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.2 cm
Package 1 Width	1.8 cm
Package 1 Length	8.5 cm
Package 1 Weight	122 g

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Halogen content performance	Halogen free product