



Main

Range of product	600 Series
Product or component type	Switch

Complementary

Control type	Rotary knob
Material	PC (polycarbonate)
Colour tint	White
Surface finish	Gloss
Installation direction	Vertical
Length	118 mm
Width	74 mm
[Ue] rated operational voltage	230/240 V
Network frequency	50 Hz
Network number of phases	1 phase
Number of gangs	1 gang
Number of poles	1
Mounting mode	Surface mounted
Fixing center	84 mm
Cable cross section	2 x 2.5 mm ² 4 x 1.5 mm ²
Quantity per set	Set of 1
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7 cm
Package 1 Width	8 cm
Package 1 Length	12 cm
Package 1 Weight	0.141 kg

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
-------------------	--