



Main

Range of product	600 Series
Product or component type	Switch
Dimmer control	Rotary push type

Complementary

Material	PC (polycarbonate)
Colour tint	White
Surface finish	Gloss
Installation direction	Vertical
Length	118 mm
Width	74 mm
Rated current	16 AX
[Ue] rated operational voltage	230/250 V
Network frequency	50 Hz
Network number of phases	1 phase
Number of gangs	1 gang
Mounting mode	Surface mounted
Fixing center	84 mm
Ambient air temperature for operation	-10...40 °C
Cable cross section	2 x 2.5 mm ² 4 x 1.5 mm ²
Quantity per set	Set of 1
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	7.7 cm
Package 1 Length	11.8 cm
Package 1 Weight	135.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information