



Main

Range of product	PDL Rowco Metal Protected Series
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Local signalling	Without light indicator
Material	Die cast aluminium
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A

Environment

IP degree of protection	IP30
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	6.4 cm
Package 1 Length	12.0 cm
Package 1 Weight	367.3 g

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Circularity Profile	No need of specific recycling operations