



Main

Range of product	Weathershield
Product or component type	Push-button
Colour	Resistant grey
Product brand	Clipsal
Device presentation	Basic element with full cover plate

Complementary

Colour code	RG
Actuator	Push-button
Contacts type and composition	1 NO for contacts close 1 NC for contacts open
Local signalling	Without light indicator
Fixing mode	By screws
Material	Plastic
Marking location	Marking on surface
[Ue] rated operational voltage	440 V AC
Inrush current	10 A
Marking	START-STOP
Mounting position	Horizontal

Environment

IP degree of protection	IP66
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.8 cm
Package 1 Width	8.8 cm
Package 1 Length	8.8 cm
Package 1 Weight	223.8 g

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations