



Main

Colour	Resistant grey
Product brand	Clipsal
Range of product	Weathershield






Complementary

Colour code	RG
Control type	Sliding type ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Mounting position	Horizontal
Fixing mode	By screws
Local signalling	Without light indicator
Material	Plastic
[Ue] rated operational voltage	250 V AC
[In] rated current	15 A
Length	115 mm
Width	85 mm
Fixing center	84 mm

Environment

IP degree of protection	IP53
Standards	AS/NZS 3112:approval number S/1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile