



Main

Range of product	Series WSF Weathershield
Product brand	Clipsal
Assembly Type	Basic element with full cover plate

Complementary

Installation Type	Flush
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	20 A
Load type	Fluorescent 16 A LEDi lamp 250 W
Mounting Type	By screws
Surface finish	Brilliant
Switch function	1-way 2-way

Environment



Standards	AS/NZS 3133 AS 60529 IEC 60669-1:approval number S/1
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.8 cm
Package 1 Width	8.8 cm
Package 1 Length	12.0 cm
Package 1 Weight	186.4 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration

RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations